

Performance Data Sheet

Omnipure Filter Company
1904 Industrial Way
Caldwell, Idaho 83605



Model K2355 DI RESIN

IMPORTANT NOTICE

Read this Performance Data Sheet and compare the capabilities of this unit with your actual water treatment needs. It is recommended that, before purchasing a water filter unit, you have your water supply tested to determine your actual water treatment needs.

NRW37SC mixed bed resin is ready to use, 1:1 chemical equivalent that is highly regenerated in the H+ and OH forms. NRW37SC resins are manufactured by a proprietary process that achieves the high purity for ultra-pure water applications such as pharmaceuticals, radiation waste, and condensate polishing. The cation and anion used in NRW-37SC are gel resins that are polymerized with a styrene-divinylbenzene matrix and functionalized.

Lab Results	
Parameter	Grains of Hardness Reduced
Filter Performance	72 Grains
	-

¹Tested using flow rate = 0.5 gpm; pressure = 60 psig; pH = 7.5 _ 0.5; temp. = 20 _ 2.5 _ C

Operating Specifications

Capacity: 72 Grains
Flow Rate: 0.50 GPM (1.9 LPM)
Maximum Pressure: 125 PSIG
Temperature: 35-100- F (2-38- C)

General Installation/Operation/Maintenance Requirements

- _ Note flow direction of filter.
- _ For quick connect fittings, push scratch free tube end into the fitting until it bottoms. **Threaded fittings must be wrapped with Teflon_ tape before installation.** Install Teflon_ taped fittings and tighten firm. Use two wrenches to firmly tighten tubing.
- _ Flush new cartridge with 5 gallons of water prior to use and check for leaks. If leaks occur, check tightness of tubing and fittings. If leaks persist, discontinue use and call your supporting dealer.
- _ Replace cartridge when rated capacity (72 Grains) is reached, or when flow becomes too slow.
- _ Install in compliance with state and local laws and regulations.

Special Notices

- _ The contaminants or other substances removed or reduced by this water treatment system are not necessarily in your water.
- _ "Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system. Systems certified for cyst reduction may be used on disinfected waters that may contain filterable cysts."

Warranty Information

Omnipure Filter Company (Omnipure) warrants that the products delivered will be free from any defects in workmanship or materials. Further, the warranty provided herein applies, only when used within the products specifications and service life, from the date of installation, beyond which time or use Omnipure is absolved of any and all liability for any use of the product. In the event of defect or non-conformity, buyer shall promptly notify Omnipure in writing, supplying proof of purchase dates, installation dates, and will protect and retain the products for investigation, or Omnipure is absolved of any and all liability for any use of the product. There are no other warranties, either merchantability or fitness, either expressed or implied.